

Eaton STS367UW64

Catalog Number: STS367UW64

Eaton shunt trip safety switch, 800 A, Three-pole, 600 Vac, 250 Vdc, Alarm switch, Auxiliary contact, 24 Vdc, 1 NO 1 NC, NEMA 4X, 304 stainless steel, Non-Fusible, 600 V

General specifications



Product Name

Eaton shunt trip safety switch

Catalog Number

STS367UW64

UPC

786685830285

Product Length/Depth

12.43 in

Product Height

71.72 in

Product Width

29.54 in

Product Weight

158 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

cUL Certified

Physical Attributes

Auxiliary contacts

Auxiliary contact

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Number Of Poles

Three-pole

Type

Shunt trip safety switch

Performance Ratings

Amperage Rating

800A

Coil voltage

24 Vdc

Protection

Non-Fusible

Voltage rating

600 Vac, 250 Vdc

Miscellaneous

Contact configuration

1 NO 1 NC

Resources

Brochures

[Shunt trip safety switch Product Aid](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

Specifications and datasheets

[Eaton Specification Sheet - STS367UW64](#)

[Shunt trip safety switch Data Sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia