

Eaton T10P48S2516

Catalog Number: T10P48S2516

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 120 x 240V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 480 delta, 150°C rise, 25 kVA, 16



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T10P48S2516
	UPC
	786680211836
Product Length/Depth	Product Height
20.36 in	37.59 in
Product Width	Product Weight
22.87 in	380 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	NEMA TP-1 efficient.

Physical Attributes

Coil material

Aluminum

Frame

818

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry type distribution ventilated transformer

Wiring connection

222C

Performance Ratings

Frequency rating

60 Hz

Primary voltage

120 x 240 V

Secondary Voltage

480 delta

Temperature rise

150 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T10P48S2516](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)