

Eaton T12M12S1516ES

Catalog Number: T12M12S1516ES

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 120V, Taps: 2 at +2.5% /4 at -2.5%, SV 120V, 150°C rise, 15 kVA, 16, ES



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T12M12S1516ES

UPC

786680210631

Product Length/Depth

18.39 in

Product Height

31.3 in

Product Width

22.89 in

Product Weight

224 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

NEMA TP-1 efficient



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Frame

816

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

120 V

Secondary Voltage

120 V

Temperature rise

150 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T12M12S1516ES](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)