

Eaton T18P11S15NV

Catalog Number: T18P11S15NV

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 208 X 416V, Taps: 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 150°C, 15 kVA, Al windings, Frame: 817N



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Totally enclosed non-ventilated transformer	T18P11S15NV
	UPC
	786680053795
Product Length/Depth	Product Height
19.5 in	37.53 in
Product Width	Product Weight
22.59 in	307 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Totally enclosed non-ventilated DS-3 or DT-3

Physical Attributes

Coil material

Aluminum

Design

DS-3

Frame

817N

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

15 kVA

Phase

Single-phase

Primary voltage

208 V, 416 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - T18P11S15NV](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia