

Eaton T20P11B1516

Catalog Number: T20P11B1516

Eaton General purpose ventilated transformer, DOE 2016, 1-phase, PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 80°C rise, 15 kVA, 8942A, 3XA



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T20P11B1516
	UPC
	786680207150
Product Length/Depth	Product Height
17.4 in	33.75 in
Product Width	Product Weight
22.45 in	234 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	DOE2016 Efficient
	Certifications
	UL Listed
	Catalog Notes
	DOE 2016 Efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

842A

Insulation

220 °C

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Wiring connection

3XA

Performance Ratings

Frequency rating

60 Hz

Kva Rating

15 kVA

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Sound Level

NEMA ST-20

Temperature rise

80 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

WS45A

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11B1516](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)