

Eaton T20P11B2516

Catalog Number: T20P11B2516

Eaton Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 80°C rise, 25 kVA, 16



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T20P11B2516
	UPC
	786680208980
Product Length/Depth	Product Height
20.36 in	37.59 in
Product Width	Product Weight
22.87 in	370 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	NEMA TP-1 efficient

Physical Attributes

Coil material

Aluminum

Frame

818

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Temperature rise

80 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11B2516](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia