

# Eaton T20P11F1516CU

Catalog Number: T20P11F1516CU

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 115°C rise, 15 kVA, 16, Copper windings



Photo is representative

## General specifications

### Product Name

Eaton General purpose ventilated transformer

### Catalog Number

T20P11F1516CU

### UPC

786680207136

### Product Length/Depth

17.4 in

### Product Height

33.75 in

### Product Width

22.45 in

### Product Weight

202 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

### Certifications

UL Listed

### Catalog Notes

DOE 2016 Efficient



Powering Business Worldwide

## Physical Attributes

### Coil material

Copper

### Enclosure

NEMA 2

### Frame

842A

### Insulation

220 °C

### Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

### Wiring connection

3XA

## Performance Ratings

### Efficiency

10 CFR Part 431-2016 (DOE 2016)

### Frequency rating

60 Hz

### Kva Rating

15 kVA

### Primary voltage

240 x 480 V

### Secondary Voltage

120/240 V

### Sound Level

NEMA ST-20

### Temperature rise

115 °C rise

### Volt ampere rating

15 kVA

## Miscellaneous

### Weathershield

WS45A

## Resources

### Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

### Specifications and datasheets

[Eaton Specification Sheet - T20P11F1516CU](#)