

Eaton T20P11F2516ESLS42

Catalog Number: T20P11F2516ESLS42

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 115°C rise, 25 kVA, 16, ES, LS42



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T20P11F2516ESLS42

UPC

786680211942

Product Length/Depth

20.36 in

Product Height

37.59 in

Product Width

22.87 in

Product Weight

375 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

NEMA TP-1 efficient, Low sound equal to 42 dB



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Frame

818

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Modification 1

Low sound 42 dB

Weathershield

WS11

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11F2516ESLS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)