

# Eaton T20P11F25NVSS

Catalog Number: T20P11F25NVSS

Totally enclosed non-ventilated transformer DS-3E Single-phase 240 x 480V 1 at +5% FCAN 2 at -5% FCBN x 2 at +2.5% FCAN 4 at -2.5% FCBN 120/240V 115°C 25 kVA Aluminum windings 818N 3XA 60 Hz



Photo is representative

## General specifications

### Product Name

Eaton General purpose ventilated transformer

### Catalog Number

T20P11F25NVSS

### UPC

786680112775

### Product Length/Depth

20.36 in

### Product Height

37.59 in

### Product Width

22.89 in

### Product Weight

407 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

### Catalog Notes

Grade 304 stainless steel enclosure (does not imply a NEMA 4X rating)  
Totally enclosed non-ventilated DS-3 or DT-3.



Powering Business Worldwide

## Physical Attributes

### Coil material

Aluminum

### Design

DS-3

### Frame

818N

### Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Totally enclosed non-ventilated transformer

### Wiring connection

3XA

## Performance Ratings

### Frequency rating

60 Hz

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

25 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - T20P11F25NVSS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)