

Eaton T20P11F3716CULS42

Catalog Number: T20P11F3716CULS42

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 115°C rise, 37.5 kVA, DOE 2016, Copper windings, 42 dB Sound



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T20P11F3716CULS42
	UPC
	786680209178
Product Length/Depth	Product Height
24.38 in	38.7 in
Product Width	Product Weight
23.51 in	321 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	DOE2016 Efficient
	Certifications
	UL Listed
	Catalog Notes
	DOE 2016 efficient

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

843A

Insulation

220 °C

Mounting

Floor

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Wiring connection

3XA

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

37.50 kVA

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Sound Level

42 dB

Temperature rise

115 °C rise

Volt ampere rating

37.5 kVA

Miscellaneous

Modification 1

Low sound 42 dB

Weathershield

WS43A

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11F3716CULS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)