

Eaton T20P11F99AF16ESLS47

Catalog Number: T20P11F99AF16ESLS47

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 115°C rise, 100 kVA, Fungus proof, 16, ESLS47



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T20P11F99AF16ESLS47

UPC

786680211508

Product Length/Depth

33.97 in

Product Height

62.88 in

Product Width

29.97 in

Product Weight

916 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Low sound design equivalent to 47 dB, NEMA TP-1 efficient, Fungus proof



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

821

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry type distribution, ventilated transformer

Wiring connection

261A

Performance Ratings

Frequency rating

60 Hz

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

100 kVA

Miscellaneous

Weathershield

WS13

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11F99AF16ESLS47](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)