

# Eaton T20P11S1516ZZ

Catalog Number: T20P11S1516ZZ

Eaton Open core-coil ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 150°C rise, 15 kVA, 16, ZZ

Photo is representative



## General specifications

### Product Name

Eaton Open core-coil ventilated transformer

### Catalog Number

T20P11S1516ZZ

### UPC

786680211409

### Product Length/Depth

1.1 in

### Product Height

1.1 in

### Product Width

1.1 in

### Product Weight

224 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

### Certifications

UL Recognized

### Catalog Notes

NEMA TP-1 efficient, Open type core and coil assembly

## Physical Attributes

### Coil material

Aluminum

### Frame

CS15G103

### Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

240 x 480 V

### Secondary Voltage

120/240 V

### Temperature rise

150 °C rise

### Volt ampere rating

15 kVA

## Resources

### Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

### Specifications and datasheets

[Eaton Specification Sheet - T20P11S1516ZZ](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)