

Eaton T20P11S15AFES16LS42

Catalog Number: T20P11S15AFES16LS42

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 150°C rise, 15 kVA, Fungus proof, ES, 16LS42



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T20P11S15AFES16LS42

UPC

786680210730

Product Length/Depth

18.39 in

Product Height

31.3 in

Product Width

22.89 in

Product Weight

228 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

NEMA TP-1 efficient Fungus proof Low sound design equivalent to 42 dB.



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Frame

816

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry type distribution ventilated transformer

Wiring connection

261A

Performance Ratings

Frequency rating

60 Hz

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11S15AFES16LS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)