

Eaton T20P11S2516ES

Catalog Number: T20P11S2516ES

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 150°C rise, 25 kVA, 16, ES



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T20P11S2516ES

UPC

786680219795

Product Length/Depth

20.36 in

Product Height

37.59 in

Product Width

22.87 in

Product Weight

361 lb

Warranty

Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

DOE 2016 efficient



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Enclosure

818

Frame

818

Insulation

220 °C

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Wiring connection

261A

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

25 kVA

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11S2516ES](#)