

Eaton T20P11S25NVSS

Catalog Number: T20P11S25NVSS

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, 1PH, PV: 240 X 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 150°C, 25 kVA, Al windings, Frame: 818N



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T20P11S25NVSS

UPC

786685223469

Product Length/Depth

20.36 in

Product Height

37.59 in

Product Width

22.89 in

Product Weight

410 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Grade 304 stainless steel enclosure (does not imply a NEMA 4X rating), Totally enclosed non-ventilated DS-3 or DT-3

Physical Attributes

Coil material

Aluminum

Design

DS-3

Frame

818N

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Volt ampere rating

25 kVA

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11S25NVSS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)