

Eaton T20P11S3716CUS6

Catalog Number: T20P11S3716CUS6

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 150°C rise, 37.5 kVA, 16, Copper windings, S6



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T20P11S3716CUS6
	UPC
	786680208577
Product Length/Depth	Product Height
20.36 in	37.59 in
Product Width	Product Weight
22.87 in	454 lb
Certifications	
Contact Manufacturer	

Performance Ratings

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Volt ampere rating

37.5 kVA

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11S3716CUS6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)