

Eaton T20P11S50NVSS

Catalog Number: T20P11S50NVSS

General-Purpose Transformer, Ventilated, DS-3, Single-phase, PV: 240 X 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 150°C, Al windings, Frame: 820N, stainless steel, 50 kVA



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T20P11S50NVSS

UPC

786680061622

Product Length/Depth

23.84 in

Product Height

42.03 in

Product Width

24.22 in

Product Weight

653 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Grade 304 stainless steel enclosure (does not imply a NEMA 4X rating), Totally enclosed non-ventilated DS-3 or DT-3



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Design

DS-3

Frame

820N

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

50 kVA

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11S50NVSS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)