

Eaton T20P11S99T16CU

Catalog Number: T20P11S99T16CU

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 150°C rise, 100 kVA, Thermal indicator, 16, CU



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T20P11S99T16CU

UPC

786680208300

Product Length/Depth

33.97 in

Product Height

62.88 in

Product Width

29.97 in

Product Weight

1040 lb

Certifications

Contact Manufacturer



Powering Business Worldwide

Performance Ratings

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Volt ampere rating

100 kVA

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T20P11S99T16CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)