

# Eaton T2235-A2-CFB09L

Catalog Number: T2235-A2-CFB09L

Eaton ATS rack PDU, 1U, (2) L5-20P input, 1.92 kW max, 110-125V, 16A, 9 ft cord, Single-phase, Outlet: (8) 5-20R

## General specifications



Product Name	Eaton ATS rack PDU	Catalog Number	T2235-A2-CFB09L
UPC	786685287287	Product Length/Depth	6 in
Product Height	23 in	Product Width	13.5 in
Product Weight	15 lb	Warranty	3 year
Compliances	Contact Manufacturer	Certifications	UL Listed

## Physical

### Mounting direction

Horizontal

### Color

Black

### Form factor

1U

### Operating Temperature

0° to 60°C (32° to 140°F)

## Electrical input

### Input connection

(2) L5-20P

### Cord length

9 ft

### Wattage

1.92 kW max

### Amperage Rating

16A

### Input voltage

110-125V

### Phase

Single-phase

### Frequency rating

50-60 Hz

## Electrical output

### Outlets

(8) 5-20R

### Circuit breaker

1P 20A

### Outlet control

No

## Additional specifications

### Series

eATS

## Resources

### Drawings

[T2235-A2-CFB09L Technical Drawing](#)

### Manuals and user guides

[Eaton T2235 series eATS ePDU](#)

### Specifications and datasheets

[Eaton Specification Sheet - T2235-A2-CFB09L](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)