

Eaton T24M29S1516

Catalog Number: T24M29S1516

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240V, Taps: 2 at +2.5% /4 at -2.5%, SV 208V, 150°C rise, 15 kVA, 16



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T24M29S1516
	UPC
	786680209468
Product Length/Depth	Product Height
18.39 in	31.3 in
Product Width	Product Weight
22.89 in	220 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	NEMA TP-1 efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

816

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry type distribution, ventilated transformer

Wiring connection

56B

Performance Ratings

Frequency rating

60 Hz

Primary voltage

240 V

Secondary Voltage

208 V

Temperature rise

150 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T24M29S1516](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)