

Eaton T24M48B25T16CU

Catalog Number: T24M48B25T16CU

Eaton Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240V, Taps: 2 at +2.5% / 4 at -2.5%, SV 480 delta, 80°C rise, 25 kVA, Thermal indicator, 16, CU



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T24M48B25T16CU
	UPC
	786680209536
Product Length/Depth	Product Height
20.36 in	37.59 in
Product Width	Product Weight
22.87 in	403 lb
Certifications	
Contact Manufacturer	

Performance Ratings

Primary voltage

240 V

Secondary Voltage

480 delta

Volt ampere rating

25 kVA

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T24M48B25T16CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)