

Eaton T24M48F1516

Catalog Number: T24M48F1516

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 240V, Taps: 2 at +2.5% /4 at -2.5%, SV 480 delta, 115°C rise, 15 kVA, 16



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T24M48F1516
	UPC
	786680210327
Product Length/Depth	Product Height
18.39 in	31.3 in
Product Width	Product Weight
22.89 in	245 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	Certifications
	UL Listed
	Catalog Notes
	NEMA TP-1 efficient

Physical Attributes

Coil material

Aluminum

Frame

816

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

240 V

Secondary Voltage

480 delta

Temperature rise

115 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T24M48F1516](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)