

Eaton T27M11E50CUEE

Catalog Number: T27M11E50CUEE

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 277V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 150°C rise [E], 50 kVA, Copper windings, EE



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T27M11E50CUEE
	UPC
	786680037238
Product Length/Depth	Product Height
0.001 in	0.001 in
Product Width	Product Weight
0.001 in	0.001 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	NEMA TP-1 efficient

Physical Attributes

Coil material

Copper

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

277 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Volt ampere rating

50 kVA

Resources

Brochures

[NEMA Premium Efficient Transformers Product Aid](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[NEMA Premium Efficient Transformers Data Sheet](#)

[Eaton Specification Sheet - T27M11E50CUEE](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)