

# Eaton T27R11S7516

Catalog Number: T27R11S7516

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 277V, Taps: 1 at +5%/2 at -5%, SV 120/240V, 150°C rise, 75 kVA, 16



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose ventilated transformer	T27R11S7516
	<b>UPC</b>
	786680208188
<b>Product Length/Depth</b>	<b>Product Height</b>
23.84 in	42.03 in
<b>Product Width</b>	<b>Product Weight</b>
24.22 in	363 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Catalog Notes</b>
	NEMA TP-1 efficient

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 2

### Frame

820

### Tap size

1 at +5% FCAN, 2 at -5% FCBN

### Type

Dry type distribution, ventilated transformer

### Wiring connection

591D

## Performance Ratings

### Frequency rating

60 Hz

### Primary voltage

277 V

### Secondary Voltage

120/240 V

### Temperature rise

150 °C rise

### Volt ampere rating

75 kVA

## Miscellaneous

### Weathershield

WS16

## Resources

### Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

### Specifications and datasheets

[Eaton Specification Sheet - T27R11S7516](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)