

Eaton T29D60F15CUNVLS50

Catalog Number: T29D60F15CUNVLS50

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 208V, Taps: 2 at +2.5% FCAN, 2 at -2.5% FCBN, SV: 600 delta, 115°C, 15 kVA, Cu windings



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T29D60F15CUNVLS50

UPC

786680028939

Product Length/Depth

0.001 in

Product Height

0.001 in

Product Width

0.001 in

Product Weight

0.001 lb

Warranty

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Totally enclosed non-ventilated DS-3 or DT-3, Low sound equal to 50 dB

Physical Attributes

Coil material

Copper

Design

DS-3

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

15 kVA

Primary voltage

208 V

Secondary Voltage

600 V

Temperature rise

115 °C rise

Miscellaneous

Modification 1

Low sound 50 dB

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - T29D60F15CUNVLS50](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)