

Eaton T29M11S2516ESLS42

Catalog Number: T29M11S2516ESLS42

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 208V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 150°C rise, 25 kVA, 16, ES, LS42



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T29M11S2516ESLS42
	UPC
	786680210839
Product Length/Depth	Product Height
20.36 in	37.59 in
Product Width	Product Weight
22.87 in	369 lb
Certifications	
Contact Manufacturer	

Performance Ratings

Primary voltage

208 V

Secondary Voltage

120/240 V

Volt ampere rating

25 kVA

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T29M11S2516ESLS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia