

# Eaton T29M24S1516CUESLS42

Catalog Number: T29M24S1516CUESLS42

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 208V, Taps: 2 at +2.5% /4 at -2.5%, SV 240 delta, 150°C rise, 15 kVA, 16, Copper windings, ESLS42



Photo is representative

## General specifications

### Product Name

Eaton General purpose ventilated transformer

### Catalog Number

T29M24S1516CUESLS42

### UPC

786680208744

### Product Length/Depth

18.39 in

### Product Height

31.3 in

### Product Width

22.89 in

### Product Weight

264 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

### Certifications

UL Listed

### Catalog Notes

NEMA TP-1 efficient, Low sound equal to 42 dB

## Physical Attributes

### Coil material

Copper

### Frame

816

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Primary voltage

208 V

### Secondary Voltage

240 delta

### Temperature rise

150 °C rise

### Volt ampere rating

15 kVA

## Miscellaneous

### Modification 1

Low sound 42 dB

### Weathershield

WS11

## Resources

### Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

### Specifications and datasheets

[Eaton Specification Sheet - T29M24S1516CUESLS42](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)