

# Eaton T29M27S1516

Catalog Number: T29M27S1516

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 208V, Taps: 2 at +2.5% /4 at -2.5%, SV 277V, 150°C rise, 15 kVA, 16



Photo is representative

## General specifications

<a href="#">Product Name</a>	<a href="#">Catalog Number</a>
Eaton General purpose ventilated transformer	T29M27S1516
	<a href="#">UPC</a>
	786680210969
<a href="#">Product Length/Depth</a>	<a href="#">Product Height</a>
18.39 in	31.3 in
<a href="#">Product Width</a>	<a href="#">Product Weight</a>
22.89 in	221 lb
<a href="#">Warranty</a>	<a href="#">Compliances</a>
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<a href="#">Certifications</a>
	UL Listed
	<a href="#">Catalog Notes</a>
	NEMA TP-1 efficient

## Physical Attributes

### Coil material

Aluminum

### Frame

816

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Primary voltage

208 V

### Secondary Voltage

277 V

### Temperature rise

150 °C rise

### Volt ampere rating

15 kVA

## Miscellaneous

### Weathershield

WS11

## Resources

### Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

### Specifications and datasheets

[Eaton Specification Sheet - T29M27S1516](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)