

Eaton T29M48S2516CU

Catalog Number: T29M48S2516CU

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 208V, Taps: 2 at +2.5% /4 at -2.5%, SV 480 delta, 150°C rise, 25 kVA, 16, Copper windings



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T29M48S2516CU

UPC

786680209369

Product Length/Depth

20.36 in

Product Height

37.59 in

Product Width

22.87 in

Product Weight

395 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

NEMA TP-1 efficient



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Frame

818

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

208 V

Secondary Voltage

480 delta

Temperature rise

150 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T29M48S2516CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)