

Eaton T29M48S5016CU

Catalog Number: T29M48S5016CU

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 208V, Taps: 2 at +2.5% /4 at -2.5%, SV 480 delta, 150°C rise, 50 kVA, 16, Copper windings



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T29M48S5016CU

UPC

786680212048

Product Length/Depth

23.84 in

Product Height

42.03 in

Product Width

24.22 in

Product Weight

616 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

NEMA TP-1 efficient



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

819

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry type distribution, ventilated transformer

Wiring connection

43G

Performance Ratings

Frequency rating

60 Hz

Primary voltage

208 V

Secondary Voltage

480 delta

Temperature rise

150 °C rise

Volt ampere rating

50 kVA

Miscellaneous

Weathershield

WS16

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T29M48S5016CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)