

Eaton T29R11B7516

Catalog Number: T29R11B7516

Eaton Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 208V, Taps: 1 at +5%/2 at -5%, SV 120/240V, 80°C rise, 75 kVA, 16



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T29R11B7516
	UPC
	786680208089
Product Length/Depth	Product Height
33.97 in	62.88 in
Product Width	Product Weight
29.97 in	878 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	NEMA TP-1 efficient

Physical Attributes

Coil material

Aluminum

Frame

821

Tap size

1 at +5% FCAN, 2 at -5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

208 V

Secondary Voltage

120/240 V

Temperature rise

80 °C rise

Volt ampere rating

75 kVA

Miscellaneous

Weathershield

WS13

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T29R11B7516](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)