

Eaton T29R11S9916CU

Catalog Number: T29R11S9916CU

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 208V, Taps: 1 at +5%/2 at -5%, SV 120/240V, 150°C rise, 100 kVA, 16, Copper windings



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T29R11S9916CU

UPC

786680209574

Product Length/Depth

33.97 in

Product Height

62.88 in

Product Width

29.97 in

Product Weight

1164 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

NEMA TP-1 efficient



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Frame

821

Tap size

1 at +5% FCAN, 2 at -5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

208 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Volt ampere rating

100 kVA

Miscellaneous

Weathershield

WS13

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T29R11S9916CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)