

Eaton T48M11B15CUNVSS

Catalog Number: T48M11B15CUNVSS

Eaton General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 80°C, 15 kVA, Cu windings, Frame: 818N



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T48M11B15CUNVSS
	UPC
	786680076985
Product Length/Depth	Product Height
20.36 in	37.59 in
Product Width	Product Weight
22.89 in	454 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

DS-3

Frame

818N

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

15 kVA

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

80 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - T48M11B15CUNVSS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)