

Eaton T48M11B3016LS42

Catalog Number: T48M11B3016LS42

Eaton Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 80°C rise, 30 kVA, 16, LS, 42



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T48M11B3016LS42

UPC

786680211331

Product Length/Depth

23.84 in

Product Height

42.03 in

Product Width

24.22 in

Product Weight

564 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

NEMA TP-1 efficient, Low sound equal to 42 dB



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Frame

819

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

80 °C rise

Volt ampere rating

30 kVA

Miscellaneous

Modification 1

Low sound 42 dB

Weathershield

WS16

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T48M11B3016LS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)