

Eaton T48M11F2516CUS6LS41

Catalog Number: T48M11F2516CUS6LS41

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 115°C rise, 25 kVA, 16, Copper windings, S6LS41



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T48M11F2516CUS6LS41

UPC

786680208775

Product Length/Depth

20.36 in

Product Height

37.59 in

Product Width

22.87 in

Product Weight

466 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Grade 316 stainless steel enclosure (does not imply NEMA 4X rating) NEMA TP-1 efficient Low sound design equivalent to 41 dB.

Physical Attributes

Coil material

Copper

Frame

818

Tap size

2 at +2.5% FCAN 4 at -2.5% FCBN

Type

Dry type distribution ventilated transformer

Wiring connection

262F

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

WS11S

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T48M11F2516CUS6LS41](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)