

Eaton T48M11F9916CULS45

Catalog Number: T48M11F9916CULS45

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 115°C rise, 100 kVA, 16, Copper windings, LS45



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T48M11F9916CULS45

UPC

786680209727

Product Length/Depth

33.97 in

Product Height

62.88 in

Product Width

29.97 in

Product Weight

1105 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Low sound design equivalent to 45 dB, NEMA TP-1 efficient



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

821

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry type distribution, ventilated transformer

Wiring connection

262F

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

100 kVA

Miscellaneous

Weathershield

WS13

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T48M11F9916CULS45](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)