

# Eaton T48M11S25CUNV

Catalog Number: T48M11S25CUNV

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 150°C, 25 kVA, Cu windings, Frame: 818N



Photo is representative

## General specifications

### Product Name

Eaton Totally enclosed non-ventilated transformer

### Catalog Number

T48M11S25CUNV

### UPC

786680055546

### Product Length/Depth

20.36 in

### Product Height

37.59 in

### Product Width

22.89 in

### Product Weight

406 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

### Catalog Notes

Totally enclosed non-ventilated DS-3 or DT-3

## Physical Attributes

### Coil material

Copper

### Design

DS-3

### Frame

818N

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

480 V

### Secondary Voltage

120/240 V

### Temperature rise

150 °C rise

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - T48M11S25CUNV](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)