

# Eaton T48M11S3716CUES

Catalog Number: T48M11S3716CUES

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 150°C rise, 37.5 kVA, 16, Copper windings, ES

Photo is representative



## General specifications

|  |                       |
|--|-----------------------|
| <b>Product Name</b>  | <b>Catalog Number</b> |
| Eaton General purpose ventilated transformer   | T48M11S3716CUES       |
|  | <b>UPC</b>            |
|  | 786680212154          |
| <b>Product Length/Depth</b>  | <b>Product Height</b> |
| 20.36 in   | 37.59 in              |
| <b>Product Width</b>   | <b>Product Weight</b> |
| 22.87 in   | 437 lb                |
| <b>Warranty</b>  | <b>Certifications</b> |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | <b>Catalog Notes</b>  |
|  | NEMA TP-1 efficient   |

## Physical Attributes

### Coil material

Copper

### Enclosure

NEMA 2

### Frame

818

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry type distribution, ventilated transformer

### Wiring connection

243D

## Performance Ratings

### Frequency rating

60 Hz

### Primary voltage

480 V

### Secondary Voltage

120/240 V

### Temperature rise

150 °C rise

### Volt ampere rating

37.5 kVA

## Miscellaneous

### Weathershield

WS11

## Resources

### Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

### Specifications and datasheets

[Eaton Specification Sheet - T48M11S3716CUES](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)