

Eaton T48M11S37CUNVLS44

Catalog Number: T48M11S37CUNVLS44

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 150°C, 37.5 kVA , Cu windings, Frame: 819N



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T48M11S37CUNVLS44
	UPC
	786680061561
Product Length/Depth	Product Height
23.84 in	42.03 in
Product Width	Product Weight
24.22 in	612 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Totally enclosed non-ventilated DS-3 or DT-3, Low sound equal to 44 dB

Physical Attributes

Coil material

Copper

Design

DS-3

Frame

819N

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

37.5 kVA

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Miscellaneous

Modification 1

Low sound 44 dB

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - T48M11S37CUNVLS44](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)