

Eaton T48M11S5016LS42

Catalog Number: T48M11S5016LS42

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 150°C rise, 50 kVA, 16, LS, 42



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T48M11S5016LS42

UPC

786680210334

Product Length/Depth

23.84 in

Product Height

42.03 in

Product Width

24.22 in

Product Weight

587 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

NEMA TP-1 efficient, Low sound equal to 42 dB

Physical Attributes

Coil material

Aluminum

Frame

819

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Volt ampere rating

50 kVA

Miscellaneous

Modification 1

Low sound 42 dB

Weathershield

WS16

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T48M11S5016LS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)