

Eaton T48M60S15NV

Catalog Number: T48M60S15NV

General-Purpose Transformer, Ventilated, Dry Type Distribution, DS-3, Single-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 600 delta, 150°C, 15 kVA, Al windings, Frame: 817N



Photo is representative

General specifications

Product Name

Eaton Totally enclosed non-ventilated transformer

Catalog Number

T48M60S15NV

UPC

786680097713

Product Length/Depth

19.5 in

Product Height

37.53 in

Product Width

22.59 in

Product Weight

325 lb

Warranty

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Totally enclosed non-ventilated DS-3 or DT-3

Physical Attributes

Coil material

Aluminum

Design

DS-3

Frame

817N

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

15 kVA

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

600 V

Temperature rise

150 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - T48M60S15NV](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)