

Eaton T48N11F3716LS42

Catalog Number: T48N11F3716LS42

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 480V, Taps: None, SV 120/240V, 115°C rise, 37.5 kVA, 16, LS, 42



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T48N11F3716LS42

UPC

786680210051

Product Length/Depth

20.36 in

Product Height

37.59 in

Product Width

22.87 in

Product Weight

388 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

NEMA TP-1 efficient Low sound design equivalent to 42 dB.

Physical Attributes

Coil material

Aluminum

Frame

818

Tap size

None

Type

Dry type distribution ventilated transformer

Wiring connection

472A

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

37.5 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T48N11F3716LS42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)