

Eaton T48N27S2516

Catalog Number: T48N27S2516

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 480V, Taps: None, SV 277V, 150°C rise, 25 kVA, 16



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	T48N27S2516
	UPC
	786680212185
Product Length/Depth	Product Height
20.36 in	37.59 in
Product Width	Product Weight
22.87 in	358 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	NEMA TP-1 efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

818

Type

Dry type distribution, ventilated transformer

Wiring connection

882A

Performance Ratings

Frequency rating

60 Hz

Primary voltage

480 V

Secondary Voltage

277 V

Temperature rise

150 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

WS11

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - T48N27S2516](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)