

Eaton T600BL-030N6F

Catalog Number: T600BL-030N6F

Eaton PWRSUPP 600 208-120/208 30kVA 60HZ w/SPD WIN, Transformer, K-Rated, NEMA 2, AB 1492-CE2 195A terminal, -10 degC to 40 degC , Gray



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Power-Suppress 600 power conditioner	T600BL-030N6F
	UPC
	743172095305
Product Length/Depth	Product Height
20 in	28 in
Product Width	Product Weight
23 in	495 lb
Certifications	
Contact Manufacturer	

defaultTaxonomyAttributeLabel

Application

Isolation, Power Conditioning

Product Category

Transformer

Special features

K-Rated

Delta input

Yes

Enclosure

NEMA 2

Frequency rating

60 Hz

Mounting

Floor

Phase

Three-phase

Surge protection

Yes

Terminals

AB 1492-CE2 195A

Type

Power conditioner

Voltage rating

208 V

Efficiency

98.79%

Input voltage

208

Load capacity

30 kVA

Number of wires

3/4

Operating Temperature

-10° to 40°C

Color

Resources

Brochures

[Eaton Power-Suppress 600 brochure](#)

Specifications and datasheets

[Eaton Specification Sheet - T600BL-030N6F](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Gray

Communication

No

Volt ampere rating

30000



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)