

# Eaton T600CL-045R6A

Catalog Number: T600CL-045R6A

Eaton PWRSUPP 600 240-120/208 45kVA 60HZ 3R 3S, Transformer, K-Rated, NEMA 3R, ILSCO TA-350 (3-L in and Out), ILSCO TA-600 (1-N Out) terminal, -10 degC to 40 degC , Gray



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Power-Suppress 600 power conditioner	T600CL-045R6A
	<b>UPC</b>
	743172094315
<b>Product Length/Depth</b>	<b>Product Height</b>
20 in	28 in
<b>Product Width</b>	<b>Product Weight</b>
23 in	700 lb
<b>Certifications</b>	
<b>Contact Manufacturer</b>	

## defaultTaxonomyAttributeLabel

### Application

Isolation, Power Conditioning

### Product Category

Transformer

### Special features

K-Rated

### Delta input

Yes

### Enclosure

NEMA 3R

### Frequency rating

60 Hz

### Mounting

Floor

### Phase

Three-phase

### Surge protection

No

### Terminals

ILSCO TA-350 (3-L in and Out), ILSCO TA-600 (1-N Out)

### Type

Power conditioner

### Voltage rating

240V

### Efficiency

98.79%

### Input voltage

240

### Load capacity

45 kVA

### Number of wires

3/4

### Operating Temperature

-10° to 40°C

### Color

## Resources

### Brochures

[Eaton Power-Suppress 600 brochure](#)

### Specifications and datasheets

[Eaton Specification Sheet - T600CL-045R6A](#)

Gray

Communication

No

Volt ampere rating

45000



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)