

Eaton T600CN-112N6

Catalog Number: T600CN-112N6

Eaton PWRSUPP 600 240-277/480 112kVA 60HZ, Transformer, K-Rated, NEMA 2, ILSCO TA-600 (3-L in), ILSCO TA-350 (3-L out), ILSCO TA-600 (1-N out) terminal, -10 degC to 40 degC , Gray



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Power-Suppress 600 power conditioner	T600CN-112N6
	UPC
	743172095008
Product Length/Depth	Product Height
32 in	38 in
Product Width	Product Weight
57 in	1210 lb
Certifications	
Contact Manufacturer	

defaultTaxonomyAttributeLabel

Application

Isolation, Power Conditioning

Product Category

Transformer

Special features

K-Rated

Delta input

Yes

Enclosure

NEMA 2

Frequency rating

60 Hz

Mounting

Floor

Phase

Three-phase

Surge protection

No

Terminals

ILSCO TA-600 (3-L in), ILSCO TA-350 (3-L out), ILSCO TA-600
(1-N out)

Type

Power conditioner

Voltage rating

240V

Efficiency

98.91%

Input voltage

240

Load capacity

112.5 kVA

Number of wires

3/4

Operating Temperature

-10° to 40°C

Resources

Brochures

[Eaton Power-Suppress 600 brochure](#)

Specifications and datasheets

[Eaton Specification Sheet - T600CN-112N6](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Color

Gray

Communication

No

Volt ampere rating

112500



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia