

Eaton T60M11E15CUEE

Catalog Number: T60M11E15CUEE

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 600V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 150°C rise [E], 15 kVA, Copper windings, EE



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T60M11E15CUEE

UPC

786680037085

Product Length/Depth

0.001 in

Product Height

0.001 in

Product Width

0.001 in

Product Weight

0.001 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

NEMA TP-1 efficient



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

600 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Volt ampere rating

15 kVA

Resources

Brochures

[NEMA Premium Efficient Transformers Product Aid](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[NEMA Premium Efficient Transformers Data Sheet](#)

[Eaton Specification Sheet - T60M11E15CUEE](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia