

Eaton T60M11S99CUEE

Catalog Number: T60M11S99CUEE

Eaton General purpose ventilated transformer, DS-3 (1-phase), PV 600V, Taps: 2 at +2.5% /4 at -2.5%, SV 120/240V, 150°C rise, 100 kVA, Copper windings, EE



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

T60M11S99CUEE

UPC

786680037078

Product Length/Depth

23.84 in

Product Height

42.03 in

Product Width

24.22 in

Product Weight

0.001 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

NEMA TP-1 efficient

Physical Attributes

Coil material

Copper

Frame

820

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

600 V

Secondary Voltage

120/240 V

Temperature rise

150 °C rise

Volt ampere rating

100 kVA

Miscellaneous

Weathershield

WS16

Resources

Brochures

[NEMA Premium Efficient Transformers Product Aid](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - T60M11S99CUEE](#)

[NEMA Premium Efficient Transformers Data Sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)