

defaultTaxonomyAttributeLabel

Type

Standard Cu/Al pressure terminals

Amperage Rating

1000 A

Voltage rating

600 V

Circuit breaker type

ND, NG, NRX NF

Frame size

Frame J-K

Color

Silver

Used with

N-frame and NRX

Interrupt rating

65 kAIC

Cable size

(3) 3/0-400 kcmil

Continuous ampere rating

1000 A

Number of wires

3

Wire size

(3) #3/0 AWG-400 kcmil

Number of poles

Single-pole

Quantity

1

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Series G MCCB quick selector](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[StrandAble terminals product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[Multi-wire lugs product aid](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

Multimedia

[Flex shaft handle installation tutorial](#)

Specifications and datasheets

[MOEM MCCB product selection guide](#)

[Eaton Specification Sheet - TA1000NB1MCWT](#)

[NG and ND-Frame molded case circuit breakers](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)