

Eaton TMC3-050-0

Catalog Number: TMC3-050-0

Eaton Crouse-Hinds series TMC3 cable gland, 0.452" - 0.660" armor min./max., Armoured and non-armoured, Aluminum, 0.50-0.78" outer sheath min./max., Industrial protection, 1/2" NPT

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series TMC3 cable gland	TMC3-050-0
	UPC
	662276887978
Product Length/Depth	Product Height
3.3 in	1.38 in
Product Width	Product Weight
1.38 in	0.25 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IECEX/ATEX

NEC hazardous rating

Class II, Division 1

Class III

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Protection type

Industrial

Gland type

Armoured and non-armoured

Cable type

MC

MC-HL

TECK

TC

TC-ER

TC-ER-HL

ITC

ITC-ER

ITC-HL

PLTC

PLTC-ER

ACIC

Material

Aluminum

Thread Size

1/2"

Thread type

NPT

Aarmor (min/max)

0.452" - 0.660"

Cable range (min/max)

0.55" - 0.78"

Outer sheath (min/max)

0.50-0.78"

Resources

Brochures

[Crouse-Hinds series TMC3 Armored Gland brochure](#)

Catalogs

[Crouse-Hinds series TMC3 Armored and Non-armored Cable Glands catalog page](#)

Certification reports

[TMC3 Armored Gland Canadian certification \(Class and Division\)](#)

[TMC3 Armored Gland Canadian certification \(Zones\)](#)

[TMC3 Armored Gland UL certification \(Class and Division\)](#)

[TMC3 Armored Gland UL certification \(Zones\)](#)

[TMC3 Armored Gland ATEX/IECEX certification](#)

[Installation instructions](#)

[IF 1890 - TMC3 Cable Gland](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - TMC3-050-0](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia